













Light is OSRAM

15.12.2020

OS-IN-2020-032

Introduction of product updates for OSOLON P1616 and OSOLON Piccolo

Objective	Introduction of product updates for OSOLON P1616 and OSOLON Piccolo		
Products affected	OSOLON P1616: SFH 4170S, SFH 4180S OSOLON Piccolo: SFH 4170S A01, SFH 4180S A01		
Background	<ul style="list-style-type: none"> • Introduction of rougher mold release foil at molding process to reduce risk of sticky units during pick & place process • Introduction of new carrier tape design to increase pocket height 		
	<table border="0" style="width: 100%;"> <tr> <td style="width: 50%; vertical-align: top;"> <p>Current status:</p> <p>Device appearance</p>  </td> <td style="width: 50%; vertical-align: top;"> <p>New status:</p> <p>Device appearance</p>  </td> </tr> </table>	<p>Current status:</p> <p>Device appearance</p> 	<p>New status:</p> <p>Device appearance</p> 
<p>Current status:</p> <p>Device appearance</p> 	<p>New status:</p> <p>Device appearance</p> 		
Realization	<table border="0" style="width: 100%;"> <tr> <td style="width: 50%; vertical-align: top;"> <p>Tape drawing</p>  <p>Pocket height: 1mm</p> </td> <td style="width: 50%; vertical-align: top;"> <p>Tape drawing</p>  <p>Pocket height: 1.1mm</p> </td> </tr> </table>	<p>Tape drawing</p>  <p>Pocket height: 1mm</p>	<p>Tape drawing</p>  <p>Pocket height: 1.1mm</p>
<p>Tape drawing</p>  <p>Pocket height: 1mm</p>	<p>Tape drawing</p>  <p>Pocket height: 1.1mm</p>		
Assessment	The datasheets will be updated accordingly by CW 01 / 2021. There is no change in the characteristics of the affected products.		
Time Schedule	Implementation: CW 01 / 2021		

Please direct your inquiry to your local Sales office.